

LowPro Summit

The original proximal lock has been improved! The new LowPro Summit Lock from Coyote Design is much easier to use and cover cosmetically. In addition to a mechanical proximal lock, the LowPro Summit also controls rotation. It is ideal for amputees with long limbs and limited space or tolerance for distal locking mechanisms.

New liner attachment is easier to glue and roll on.

New tab is easier to engage.

New LowPro lock is glued to the inside of the socket, making it much easier to engage and cover.

No space is required for the lock distally, maximizing clearance for the knee center. Use the socket adaptor of your choice.

Works with most fabric backed liners.
No need to purchase a locking liner.

The LowPro Summit Lock is shown here with the Ossur Seal-In Liner, and CQL Valve from Coyote.



LowPro Summit Lock: **CD102**
Adhesive sold separately: **CD4120**

Patent # 6666894, other patents pending.



Customer Service or Technical Support: (800) 819-5980 • (208) 429-0026

New tips and help available online: www.coyotedesign.com